

# Base Blind Corner Cabinet Installation Notes

1 – Actual cabinet dimension is 3” less than nomenclature (i.e. B42BCD is 39” wide)

2 – Pull cabinet as specified on plan provided by designer from the corner of adjacent wall.

3 – Your blind corner cabinet is shipped with an attached 7” wide slab overlay panel, w/ edges matching door edges.

4 – to create a 90 filler, remove the overlay panel, split it in half then miter the two panels together. Use a backer filler on the return so the overlay is flush with the adjacent cabinet doors as shown.

